






Date: January 8, 2007

Philips Lighting Electronics N.A.

10275 West Higgins Road
Rosemont, IL 60018

ELECTRONIC FLUORESCENT BALLASTS - EXTERNAL FUSE RECOMMENDATIONS

	Indicates 120 -277 volt		Indicates 120 volt
	Indicates 277 volt		Indicates 347 volt
	Indicates 347-480 volts		

		Ballast Family Part Number	Minimum Fuse Recommendation (Amps)	
			Fast Acting	Slo-Blow
Compact fluorescent	13W	ICF-2S13-XX-XX	7	3
		ICF-2S13-XX-XX-QS		
		RCF-2S13-XX-XX-QS		
		RMB-1P13-XX		
		RMB-1P13-S2-H		
		RMB-2P13-XX		
	RMB-2P13-S3-H			
	18W	ICF-2S18-XX-XX	7	3
		ICF-2S18-XX-XX-QS		
		RCF-2S18-XX-XX-QS		
		REB2S18-M1-XX-DIM		
		REZ-1Q18-M2-XX		
		VEZ-1Q18-M2-XX		
	REZ-2Q18-M2-XX			
	VEZ-2Q18-M2-XX			
	26W	ICF-2S26-XX-XX		
		ICF-2S26-XX-XX-QS		
		RMB-1P26-S2		
RCF-2S26-XX-XX-QS				
REB2S26-M1-XX-DIM				

		REZ-2Q26-M2-XX	7	3
		VEZ-2Q26-M2-XX		
	42W	IZT-2S26-M5-XX		
		REZ-1T42-M2-XX		
		REZ-2T42-M3-XX		
		VEZ-1T42-M2-XX		
		VEZ-2T42-M3-XX		
		ICF-2S42-90C-XX-XX		
		ICF-2S42-XX-XX		
		IZT-2T42-M5-XX		
		IZT-2S26-M5-XX		
		70W		
	ICF-2S70-M4-BS			
	120W	ICF1H120-M4-LS		
		ICF1H120-M4-BS		
	39W	REL-1TTS39		
REL-2TTS39				
VEL-1TTS39				
VEL-2TTS39				
40W	RCN-1TTP40-SC	7	3	
	RCN-2TTP40-SC			
	RCN-3TTP40-SC			
	VCN-1TTP40-SC			
	VCN-2TTP40-SC			
	VCN-3TTP40-SC			
	GCN-2TTP40-SC			
	REL-1TTS40			
	REL-2TTS40			
	VEL-1TTS40			
	VEL-2TTS40			
	IZT-2TTS40-SC			
	REZ-1TTS40-SC			
	REZ-2TTS40-SC			
	VEZ-1TTS40-SC			
	VEZ-2TTS40-SC			
	RZT-1TTS40			
	RZT-2TTS40			
	VZT-1TTS40			
VZT-2TTS40				
50 W	REL-1TTS50	7	3	

		VEL-1TTS50		
		REL-2TTS50		
		VEL-2TTS50		
T5		ICN-2S28	7	3
		ICN3S14-D		
T5 HO Linear		ICN-2S24	7	3
		IEZ-124-D		
		IEZ-2S24-D		
		ICN-2S39		
		ICN-2S54		
		ICN-2S54-90C		
		ICN-1S80		
		VZT-180	8	5
		ICN-4S54-90C-2LS		
		ICN-4S54-90C-2LS-G	7	3
		HCN-2S54-90C		
		HCN-4S54-90C-2LS-G		
		REZ-154		
		VEZ-154		
		REZ-2S54		
		VEZ-2S54		
		RZT-154		
		RZT-2S54		
		VZT-154		
		VZT-2S54		
T8		All ballasts for four foot and smaller T8 lamps – rapid start and instant start REL,VEL,ICN,IOP,RCN,VCN,ROP, REZ, VEZ, RXT, VZT, IZT, IEZ	7	3
T8 and T12 H.O.		ICN-2S86	8	5
		REL-2S86		
		VEL-2S86		
		REL-2S110		
		VEL-2S110		
T8 and T12 Slimline		REL-2P59-SC	7	3
		VEL-2P59-SC		
		IOP-2P59-SC		
		RCN-2P59		
		VCN-2P59		
		GEL-2P59		

	REL-2P60-S		
	REL2P60-SA		
	VEL-2P75-S		

Please note: All external fuses should be properly rated for the voltage being utilized.